

# Q-Stress

## PRIMARY BENEFITS:

- **Logical user interface:** The system's left-to-right navigation and intuitive controls guide users through procedures with ease.
- **Improved trace quality:** Our innovative Source Consistency Filter (SCF) minimizes noise and baseline artifact while preserving a diagnostic-quality ECG signal.
- **Wireless freedom:** The Wireless Acquisition Module (WAM™) digitally transmits ECG data, providing comfort and freedom of movement for the patient.
- **12-Lead ECG interpretation:** Best-in-class VERITAS™ algorithm provides 12-Lead ECG interpretation for adults, adolescents and children.



## A UNIQUE APPROACH TO CLINICAL DATA

Q-Stress®, brought to you by Mortara, is designed to provide comprehensive clinical information to meet the ever-changing demands of today's diverse patient population, from routine exams to complex cardiac evaluations.

- Quickly access continuous ST trends and profile, ST level and slope for all 12 average complexes, and auto comparison with reference complexes.
- Enhanced full disclosure mode provides a beat-by-beat review during the exam, as well as post-test, allowing easy retrospective addition of events and ECG printing.

## A SOLUTION DRIVEN DESIGN TO ENHANCE YOUR WORKFLOW

Designed by clinicians for clinicians, the powerful graphical user interface paired with our 24-inch widescreen color touch display works with you - the way you work.

- Begin by importing your patients' demographics. This fast and simple step enables you to eliminate manual data entry, streamline your work, and minimize documentation and billing errors.
- Append significant data points as needed to the final report.
- Configured with our TM55 or TM65 treadmill, Q-Stress will ensure you're fully equipped for top performance. Our medical treadmills have been the industry's gold standard for more than three decades and are among the best selling in the world.

## A CONNECTIVITY OPTION THAT'S RIGHT FOR YOU

From simple connectivity to complete interoperability, Q-Stress offers a variety of integration solutions.

- Communication choices include PDF, XML, HL7, and DICOM®.
- Combine stress data with other systems that use non-proprietary formats, including your echo and nuclear imaging systems.
- Share final reports, access shared printers, and archive information to your EHR.





Q-STRESS®

**MORTARA INSTRUMENT, INC.**

7865 North 86th Street  
Milwaukee, WI 53224  
U.S.A.

Tel: 414.354.1600

Tel: 800.231.7437

Service: 888.MORTARA

Fax: 414.354.4760

**MORTARA INSTRUMENT EUROPE S.R.L.**

(European Headquarters)

Via Cimarosa 103/105  
40033 Casalecchio di Reno (BO)  
Italy

Tel: +39.051.298.7811

Fax: +39.051.613.3582

**MORTARA INSTRUMENT AUSTRALIA**

PO Box 7568

Baulkham Hills NSW 2153

Unit 28, 9 Hoyle Avenue

Castle Hill NSW 2154

Australia

Tel: +61 2 8070 9303

Fax: +61 2 9899 9478

**MORTARA INSTRUMENT UK LTD**

Units 11 & 12, Scion House

Stirling University Innovation Park

Stirling FK9 4NF

Scotland

Tel: +44.1786.444980

Fax: +44.1786.446630

[www.mortara.com](http://www.mortara.com)

ISO 13485 CERTIFIED



**WARRANTY + SERVICE**

Mortara Instrument is committed to the highest level of customer support. Please contact us for the program which best suits your needs.

\*Specifications subject to change without notice.

Burdick®, Mortara®, Q-Stress®, Quinton®, VERITAS™ and WAM™ are trademarks or registered trademarks of Mortara Instrument, Inc.

Microsoft® and Windows® are registered trademarks of Microsoft Corp.

SunTech® and Tango® are registered trademarks of SunTech Medical, Inc.

DICOM® is the registered trademark of the National Electrical Manufacturers Association for its standards publications relating to digital communications of medical information.

2016-01

FEATURE	SPECIFICATION*
<b>OPERATING SYSTEM</b>	Microsoft® Windows® 7 Professional 64-bit
<b>POWER REQUIREMENTS</b>	100/120 VAC 50/60 Hz 2.5 A nominal; 200/240 VAC 50/60 Hz 1.3 A nominal
<b>PROTOCOLS</b>	<b>STANDARD</b> — Bruce, Modified Bruce, Modified Balke, Naughton, USAF/SAM 2.0, USAF/SAM 3.3, Ramped-low, Ramped-medium, Ramped-high, Time-Ramp, and METs Ramp, Astrand (ergometer), pharmacological and more <b>CUSTOM</b> — Up to 100 custom protocols supported
<b>FRONT END MODULE</b>	AM12Q with AHA 10-electrode-pinch or snap connectors AM12Q with IEC 10-electrode-pinch or snap connectors WAM™ for wireless ECG acquisition with AHA 10-electrode-pinch connectors WAM for wireless ECG acquisition with IEC 10-electrode-pinch connectors
<b>ECG</b>	<b>LEAD GROUPS</b> — Standard (Mason-Likar), Cabrera 12-lead <b>DISPLAY FORMAT</b> — 3, 6, 6x2, or 12x1 channels <b>PERFORMANCE STANDARD</b> — AAMI-EC11: gain accuracy, frequency response, CMRR, system noise, dynamic range, and input impedance
<b>DISPLAY AND ANALYSIS FILTERS</b>	Source Consistency Filter (SCF), muscle artifact, baseline wander, 40 Hz low pass, line frequency
<b>REPORTS</b>	<b>IN-TEST</b> — 12-lead, average beat report, 1-page write screen, continuous rhythm, arrhythmia events <b>FINAL</b> — Summary, tabular, worst case, average beats by stage or by minute, in-test ECG reports, trend graphs and peak exercise. Reports can be viewed, printed, saved in PDF format, emailed or exported in PDF, XML and DICOM. <b>CUSTOM</b> — Unlimited customizable reports
<b>OUTPUTS</b>	TTL pulse and analog signals for QRS detection synchronization using any ECG lead
<b>EXTERNAL DEVICE INTERFACES</b>	<b>TREADMILLS</b> — Quinton TM 55/65, Trackmaster TMX428 and TMX425 <b>ERGOMETERS</b> — Compatible with Ergoline and Lode communication protocols <b>BLOOD PRESSURE MONITORS</b> — SunTech® Tango®+ and Tango M2
<b>PRINTERS</b>	<b>THERMAL</b> — High-resolution Z200+ with automatic feed and continuous printing capability (requires additional network port) <b>LASER</b> — Optional compact HP M401n laser printer with high quality print (recommended) <b>PAPER</b> — 8.5 x 11" (letter) or 210 x 300 mm (A4)
<b>NETWORK INTERFACE</b>	Microsoft-compatible networking for storage, distribution and email; 100 Mbps connection or better is required
<b>EXPORT/COMMUNICATION PROTOCOL/FORMAT</b>	TCP/IP, PDF, XML, HL7, DICOM
<b>REMOTE TECHNICAL SERVICE INTERFACE</b>	Remote service increases system uptime availability and decreases the user's requirement to assist the troubleshooting process. Available via network or desktop connections (only in the US).
<b>DISPLAY</b>	24" (609 mm) flat panel LCD; 24" touchscreen display is optional
<b>CART DIMENSIONS AND WEIGHT</b>	36 x 30 x 20" (914 x 762 x 508 mm); 150 lb (68 kg); (weight varies based on cart options)
<b>WARRANTY</b>	13 months parts and labor
<b>OPTIONS</b>	Networking, Resting ECG Analysis, ST-segment Re-Analysis, TTL Trigger, WAM
<b>ORDERING INFORMATION — ACCESSORIES</b>	
9922-020-50	SunTech Tango M2 BP Monitor Kit for Q-Stress
9922-017-52	SunTech Tango+ and Tango M2 SpO2 option
9100-026-60	Thermal Paper, Z200+, Z-fold, full grid, 8.5 in x 11 in., 12 packs/case
9100-026-61	Thermal Paper, Z200+, Z-fold, full grid, A4 format, 210mm x 300mm; 12 packs/case